




PHILIPS


HR2541, HR2542
HR2543, HR2545
HR2546




HR2541
HR2542
HR2543
HR2545




HR2543
HR2545



HR2546


















HR2545
HR2546











HR2542
HR2543



HR2543
HR2545



HR2546













HR2542
HR2543



HR2545
HR2546






		Kg (MAX)	⌚	⚙️
		100-200 g	30 sec	TURBO
		100-400 ml	60 sec	①
		100-500 ml	60 sec	①
		100-500 ml	60 sec	①
		250 ml	70-90 sec	TURBO
		4 x	120 sec	TURBO
		250 ml	70-90 sec.	TURBO
		4 x	2 min.	TURBO
		750 g	3 min.	TURBO
		750 g	2 min.	①

		Kg (MAX)	⌚	⚙️	
		100 g	5 x 1 sec.	①	
		120 g	5 sec.	TURBO	
		20 g	5 x 1 sec.	①	
		100 g	20 sec.	TURBO	
		200 g	5 x 1 sec.	①	
		200 g	10 sec.	TURBO	
		30 g	5 x 1 sec.	①	
		200 g	30 sec.	TURBO	
		100 g	20 sec.	TURBO	
		80 g	30 sec.	TURBO	



	⚙️	⌚	⚙️
	✗	✗	✓
	✓	✗	✓
	✗	✗	✓
	✓	✓	✓
	✗	✗	✓
	✓	✓	✓
	✓	✓	✓
	✓	✓	✓



Дополнение к эксплуатационной документации
Қосымша пайдалану құжаттамасын